

Electronic quick probe for external measurements

For grooves and thicknesses

Kroepelin
Längenmesstechnik

Application:

For measuring thicknesses, wall thicknesses and external grooves.

Execution:

- Large, high-contrast LCD display (digit size 8.5 mm)
- Combined digit and scale display
- mm/inch switch-over
- Measuring mode ABSOLUTE
- Measured value classification (red/green display)
- 1 fixed and 1 movable measuring arm
- Digital version: Scale interval can be switched: 0.001/0.002/0.005/0.01/0.02/0.05 mm

Advantage:

- Measured result can be read directly

Delivery:

With traceable test certificate in box



Art. no.	33241 031
Brand	KROEPLIN
Manufacturer Part Number	K220
IP protection class	IP 67
Min./max. length measuring range	0-20 mm
Digit increment	0.01 mm
Display	Digital
Measuring depth	85 mm
Type	K220
Measuring arrangement	6
Measuring contact length movable	24.7 mm
Measuring contact length fixed	24.6 mm
Number of rechargeable batteries/batteries	2 PCS
Battery designation	Micro AAA; R03; UM4
Gross Weight	0.300 kg
Product Group	332