



MASTER GLASS LED candles and lusters



MAS LEDLusterDT5.9-60W E14 927 P45 CL G

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lusters with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cozy atmosphere. The MASTER LED candles and lusters can be dimmed for different lumen level and also for the different color temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED and provides excellent quality of light. By offering a lifetime of 25,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Luminous Flux	806 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	136 lm/W
Color Consistency	<6
Color rendering index (CRI)	90

LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM)	0.9
Stroboscopic effect value (SVM)	0.4
Photobiological safety according to EN	RG0
62471	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.9 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V


Datasheet, 2023, November 23 data subject to change

MASTER GLASS LED candles and lusters

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	1109149


EyeComfort	Yes
Product Data	
Order product name	MAS LEDLusterDT5.9-60W E14 927 P45
	CL G
Full product name	MAS LEDLusterDT5.9-60W E14 927 P45
	CLG
Full product code	871951444961900
Order code	929003014182
Material Nr. (12NC)	929003014182
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514449619
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514449626

Dimensional drawing




Product	D	С
MAS LEDLusterDT5.9-60W E14 927 P45 CL G	45 mm	80 mm

Photometric data




Light Distribution Diagram - MAS LEDLusterDT5.9-60W E14 927 P45 CL G



Spectral Power Distribution Colour - MAS LEDLusterDT5.9-60W E14 927 P45 CL G

MASTER GLASS LED candles and lusters


Photometric data




Calculus Presentation 4.5 Philips Lighting B.V. Page: 17

General uniform lighting - MAS LEDLusterDT5.9-60W E14 927 P45 CL G

Lifetime





Life Expectancy Diagram - MAS LEDLusterDT5.9-60W E14 927 P45 CL G

Lumen Maintenance Diagram - MAS LEDLusterDT5.9-60W E14 927 P45 CL G



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.