

### Bezeichnung


### Maßzeichnung

### Polzahl

### von hinten verschraubbar

### von vorn verschraubbar

Flanschstecker, mit Litzen




von hinten verschraubbar

von vorn verschraubbar

3 x 0,25	09 3419 00 03	09 3419 86 03
4 x 0,25	09 3421 00 04	09 3421 86 04
5 x 0,25	09 3425 00 05	09 3425 86 05
6 x 0,14	09 3423 00 06	09 3423 86 06
8 x 0,14	09 3427 00 08	09 3427 86 08

Flanschstecker, von vorn verschraubbar, tauchlöten




### Polzahl

### Bestell-Nr.

3	09 3403 81 03	
4	09 3391 81 04	
6	09 3463 81 06	
8	09 3487 81 08	


Flanschstecker, von vorn verschraubbar, tauchlöten, mit Schirmblech



Leiterplattendicke: 1,6 mm

3	09 3419 81 03
4	09 3421 81 04
5	09 3425 81 05
6	09 3423 81 06
8	09 3427 81 08


Flanschstecker, gewinkelt, von vorn verschraubbar, tauchlöten, mit Schirmblech



Leiterplattendicke: 1,6 mm

3	09 3419 82 03
4	09 3421 82 04
5	09 3425 82 05
6	09 3423 82 06

Flanschstecker, gewinkelt, von vorn verschraubbar, tauchlöten




Leiterplattendicke: 1,5 mm



3	99 3403 282 03
4	99 3391 282 04

Flanschstecker, von vorn verschraubbar, mit Ethernetkabel



### Polzahl

### Kabellänge

### Bestell-Nr.

4	0,5 m	70 3421 005 04
---	-------	----------------

**NEU**