

DATABLAD - 3P 10X38MFH30A 600V MIDGET - INDICATOR



Sikringsholder, Lav spenning, 32 A, AC 690 V, 10 x 38 mm, 3P, UL, IEC, med indikator



Powering Business Worldwide™

Type **3P 10X38MFH30A 600V Midget - indicator**
Catalog No. **CHM3DIU**

Leveringsprogram

Produktspekter			Smeltesikring tilbehør
Basisfunksjon			Sikringsholder
Bruksområde			Lav spenning
Nominell strøm	I	A	32
Nominell spenning			AC 690 V
Størrelse			10 x 38 mm
Statusindikator			med indikator
Beskrivelse			DIN-skinne fargekodet Normert for bruk med 75 °C eller 90 °C ledning flettet ledning reserveklemmer og med kamsamleskinner Bruk en kabel som er beregnet for høyere temperatur med passende belastningsreduksjon. modulær
Antall poler			3P
kan brukes før størrelse/applikasjoner			for sylindersikringskassetter for minisikringer
Standard/Godkjennelse			UL IEC
Standarder/Regulations			IEC cULus CCC CSA UR

Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss8.1-27-14-21-21 [ADI305004])			
For fuse size			10x38 mm
Number of poles			3
Concurrently switching N-neutral			No