

WIB 6

Circular Surface Sealed Boxes with 4 x M20 cones



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.



Material	Thermoplastic
Protection class	IP55
Temp. range min	-25 °C
Temp. range max	85 °C
Glow wire test	650 °C
Impact resistance	IK07
External dimensions LxWxH	77x40mm
Type	WIB 6
Product Color	RAL 9005
Order no. UK	665N
Packing unit	8

Description:

Circular box with 4xM20 cones



Easy opening

21.03.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

 +44-12-08816062 ·  +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk