



Reset remote, 110-125VAC/DC

Part no. **IZMX-RR110AD-40-1**
 Article no. **184126**
 Catalog No. **68D2806G61**

Delivery programme

Product range			Accessories
Accessories			Trip indication / Reset options
Accessories			Remote reset
			The circuit-breaker is equipped with a mechanical trip indicator (red pin). After the remote reset coil is electrically actuated, the reclosing lockout can be reset. Cannot be combined with remote reset.
Rated control voltage	U _s	V	110 - 127 V AC 50/60 Hz 110 - 125 V DC
For use with			IZMX40...W IZMX40...F

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70

Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Shunt release (for power circuit breaker) (EC001023)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Full load current trip (ecl@ss8.1-27-37-04-18 [AKF016010])			
Rated control supply voltage U _s at AC 50HZ		V	110 - 127
Rated control supply voltage U _s at AC 60HZ		V	110 - 127
Rated control supply voltage U _s at DC		V	110 - 125
Voltage type for actuating			AC/DC
Initial value of the undelayed short-circuit release - setting range		A	0
End value adjustment range undelayed short-circuit release		A	0
Type of electric connection			Flat plug-in connection
Number of contacts as normally open contact			0
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			0
Suitable for power circuit breaker			Yes
Suitable for off-load switch			Yes
Suitable for motor safety switch			No
Suitable for overload relay			No