



Part no.: 50111225
KB JST-M12A-8P-3000
Connection cable



Figure can vary

Contents

- Technical data
- Electrical connection

Technical data

Basic data	
Suitable for interface	RS 232

Connection	
Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial

Connection 2	
Type of connection	JST ZHR
No. of pins	10 -pin 6 -pin

Cable properties	
Number of conductors	8 Piece(s)
Sheathing color	Black
Shielded	Yes
Cable design	Interconnection cable
Cable diameter (external)	6 mm
Cable length	3,000 mm
Sheathing material	PUR

Classification	
Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial

Connection 2	
Type of connection	JST ZHR
No. of pins	10 -pin 6 -pin