



SVS ECO VALVE PLUG FORM A 18MM 250V

3+PE field-wireable M20x1,5

Form A (18 mm) for pressure switch
0...230 V AC/DC, without components
M20 × 1.5 mm
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Height: 31 mm

Product may differ from Image

Approvals



Form

29405

Technical Data

Contact figure	Cable outlet can be turned in 90° steps
Operating voltage	0...230 V AC/DC
Compression gland	M20 × 1.5 mm
Connection cross section	0.5...1.5 mm ²
Sealing range (cable diameter)	8...10 mm
Protection	IP65 inserted and tightened
Locking of ports	M3 (recommended torque 0.4 Nm)

General data

Temperature range	-25...+80 °C
-------------------	--------------

Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1