



Figure similar

POWER SUPPLY; PHASES:3; PN(KW):0,864;  
 UPRI(V):575-500-460-400-230- 200; USEC(V DC):24;  
 ISEC(A DC):36/43 (60/40 CEL); F(HZ):50...60; VECTOR  
 GR./SHIELD WNG.:YY0 /0; PROTECTION CL.:I;  
 TA/SOKL:60 /B; W(%):4,2; IP00; TYPE OF  
 TERMINALS:SCREW CONNECTION;  
 INSTALLATION:SCREW; EN 61558-2-6, EN61131-2  
 >UL/CSA-RECOGNIZED< >SAFETY ISOLATING  
 TRANSFORMER<

**Inputs:**

Type of electrical connection at input for main current circuit	screw-type terminals
---	----------------------

**Outputs:**

<b>Output voltage</b>		
• _1 Rated value	V	24
Output voltage of the measurement signal at analog output for DC maximum	V	28.8
Output voltage of the measurement signal at analog output for DC minimum	V	20.4
<b>Output current</b>		
• _1 Rated value	A	36

**Mechanical data:**

Mounting type	screws
---------------	--------

**Certificates/ approvals:**

General Product Approval	Shipping Approval	other
--------------------------	-------------------	-------



[Declaration of Conformity](#)

**Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)  
<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4AV34022FB000C>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AV34022FB000C>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=4AV34022FB000C&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=4AV34022FB000C&lang=en)

last modified:

16.03.2015