



VT-7632 GLASS GU10 WALL FITTING, STAINLESS STEEL BODY- 2 WAY  
IP44

Dimensions  
**110x60x178mm**

SKU:7504

**2** YEARS  
WARRANTY



## Technical Information

Holder Type: 2XGU10

Rated Load: Max 2x35W

Unit Color: STAINLESS STEEL

Body Type: Stainless Steel

IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50Hz

## Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.69
Unit CBM	0.0016625

### Listing Details

EAN Code	3800157617635
Commodity Code	9405109890

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	480

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES