

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1200655109**
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Single-Ended Cordset, 12 Poles, Male (90°) to Pigtail, 26 AWG, PUR Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
 Series 120065
 Connector End A Micro-Change (M12)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview Brad Micro-Change (M12) Connectors
 Product Name Micro-Change (M12)
 Protocol N/A
 Region Europe
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 884982224292

Physical

Cable Diameter 6.00mm (.236")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Male-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PUR
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Net Weight 102.499/g
 Orientation 90° to Pigtail
 Poles 12
 Temperature Range - Operating -25° to +80°C
 Wire Size AWG 26
 Wire/Cable Type UL 20549

Electrical


Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V AC/DC

Material Info

Engineering Number 80C007H45M020

Reference - Drawing Numbers

Sales Drawing 1200655109-000



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000410038_00_000.pdf

CER_4000410299_00_000.pdf

Search Parts in this Series

120065 Series

This document was generated on 11/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION