

## DSUB SV FE TSDC 50P AU3



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 050 4704
Specification	DSUB SV FE TSDC 50P AU3
HARTING eCatalogue	<a href="https://b2b.harting.com/09670504704">https://b2b.harting.com/09670504704</a>

### Version

Termination method	Solder cup termination
Gender	Female
Size	D-Sub 5
Connection type	PCB to cable Cable to cable
Number of contacts	50
Locking type	Fixing flange with feed through hole $\varnothing$ 3.1 mm

### Technical characteristics

Conductor cross-section	0.5 mm <sup>2</sup> max.
Conductor cross-section	AWG 20
Rated current	7.5 A
Clearance distance	$\geq$ 1 mm
Creepage distance	$\geq$ 1 mm
Insulation resistance	$>10^{10}$ $\Omega$
Contact resistance	$\leq$ 10 m $\Omega$
Stripping length	2.5 ... 3 mm
Limiting temperature	-55 ... +125 °C (Soldering iron temperature during soldering: max. 350 °C for 3-5 s)
Insertion force	$\leq$ 167 N
Withdrawal force	$\geq$ 14.5 N $\leq$ 111 N
Performance level	3
Mating cycles	$\geq$ 50



Pushing Performance  
Since 1945

## Technical characteristics

Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, tin plated
Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079

## Commercial data

Packaging size	50
Net weight	20.5 g
Country of origin	Germany
European customs tariff number	85366990



**Pushing Performance**  
Since 1945

## Commercial data

GTIN	5713140093621
eCl@ss	27440214 D-Sub coupler