

Platform trolley series 600, 2 front walls, zinc plated

The surface of the loading area is covered with sheet steel, load capacity 500 kg



Execution:

- The surface of the loading area is covered with 2 mm electrolytically zinc-plated sheet steel
- Loading area height 260 mm
- Front walls made of melamine-coated MDF board, height 400 mm
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- The 600 series includes platform trolleys, table trolleys, platform trolleys with front wall, box trolleys and bar-type trolleys.

Art. no.	50260 025
Brand	KONGAMEK
Manufacturer Part Number	KM633-3
Type	With front and rear wall
Load-carrying capacity	500 kg
Length	1000 mm
Width	700 mm
Height	900 mm
Loading surface length	1000 mm
Loading surface size	1000 x 700 mm
Loading-surface width	700 mm
Material of loading surface	Steel plate
Colour	Silver coloured
Surface	Zinc plated
Number of steering rollers	2
Number of fixed rollers	2
With wheel lock	No
Wheel diameter	200 mm
Material of wheel	Solid rubber
Made in	Sweden
Gross Weight	49.000 kg
Product Group	5AT



EAN

7350050352349