

## Electronics side cutters ESD

Round head, with chamfer and wire clamp



### Application:

For delicate cutting tasks in electronics and precision mechanics fields.

### Execution:

- Ball bearing chrome steel
- Blades also inductively hardened
- Robust, box and clearance-free joint
- Low-friction double spring for smooth, even opening action

### Advantage:

- Mirror-finished surface with fine oil film to protect against rust, no interference in the circuit by flaking chrome parts
- Safe, ergonomic and fatigue-free working thanks to two-component handles
- ESD design, discharges electricity



<b>Art. no.</b>	<b>53106 080</b>
<b>Brand</b>	KNIPEX
<b>Manufacturer Part Number</b>	77 12 115 ESD
<b>Length</b>	115 mm
<b>Max. soft wire diameter cutting capacity</b>	1.6 mm
<b>Head design</b>	Round, With small bevel
<b>Surface</b>	Plain
<b>Material of handle</b>	2-component plastic
<b>ESD-capable</b>	Yes
<b>Gross Weight</b>	0.081 kg
<b>Product Group</b>	535

### EAN

4003773025108