

SHARXS HTI 1500 W/D7/60

SharXS HTI | Metal halide lamps, double-ended



Product datasheet

Technical data


Electrical data

Nominal wattage	1500.00 W
Nominal voltage	110 V
Ignition voltage	5.0 / 35 kVp
Nominal current	14.0 A
Lamp current	14.0 A

Photometrical data

Nominal luminous flux	145000 lm
Luminance	42000 cd/cm ²
Color temperature	6000 K
Color rendering index Ra	90

Dimensions & weight



Diameter	25.0 mm
Length	135.0 mm
Light center length (LCL)	57.5 mm

Temperatures & operating conditions

Maximum permitted pinch temperature	450 °C
-------------------------------------	--------

Lifespan

Lifespan	750 h
----------	-------

Additional product data

Base (standard designation)	SFc10-4
Product remark	May be operated from 1,200...1,500 W

Product datasheet

Capabilities

Burning position	Any
------------------	-----

Certificates & standards

EEL – Energy Label	B
--------------------	---

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321285294	OSRHTI1500D760	-	-	-

Product datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, Baby SharXS HTI, SharXS HTI and Maxi SharXS HTI lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321285294	SHARXS HTI 1500 W/D7/60	Shipping carton box 1	245 mm x 59 mm x 100 mm	1.45 dm ³	126.00 g
4008321285300	SHARXS HTI 1500 W/D7/60	Shipping carton box 10	262 mm x 317 mm x 214 mm	17.77 dm ³	1474.00 g
4008321349569	SHARXS HTI 1500 W/D7/60	Shipping carton box 30	256 mm x 176 mm x 125 mm	5.63 dm ³	1384.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
