



BE-8904 - BE-8945

**ERGO™ TORX® Screwdrivers with
Rubber Grip Double Handle T4-T45**



PRODUCT DETAILS









- Screwdriver developed according to the scientific ERGO™ process
- For TORX® head screws
- Phosphate finished tip for higher accuracy
- three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Maximum comfort with minimum effort thanks to an ergonomic design
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- Integrated hanging hole
- Flat face to prevent rolling away
- High-performance alloy steel blade with chrome plating, entirely hardened for high protection against corrosion, long life tool



Follow the Fish!



PRODUCT ATTRIBUTES

Product								
BE-8904	T 4	1,30 mm	75 mm	2.5 mm	17 mm	103 mm	178 mm	30 g
BE-8905	T 5	1,37 mm	75 mm	2.5 mm	17 mm	103 mm	178 mm	31 g
BE-8906	T 6	1.65 mm	75 mm	3 mm	17 mm	103 mm	163 mm	31 g
BE-8907	T 7	1.97 mm	75 mm	3 mm	17 mm	103 mm	178 mm	31 g
BE-8908	T 8	2.30 mm	75 mm	3 mm	17 mm	103 mm	178 mm	31 g
BE-8909	T 9	2.48 mm	75 mm	3 mm	17 mm	103 mm	178 mm	31 g
BE-8910	T 10	2.72 mm	75 mm	3 mm	20 mm	122 mm	197 mm	31 g
BE-8915	T 15	3.26 mm	100 mm	4 mm	27 mm	122 mm	222 mm	57 g
BE-8920	T 20	3.84 mm	100 mm	4 mm	27 mm	122 mm	222 mm	57 g
BE-8925	T 25	4.40 mm	125 mm	6 mm	27 mm	122 mm	247 mm	70 g
BE-8927	T 27	4.96 mm	125 mm	6 mm	27 mm	122 mm	247 mm	70 g
BE-8930	T30	5.49 mm	150 mm	6 mm	36 mm	122 mm	272 mm	119 g
BE-8940	T40	6.60 mm	150 mm	7 mm	36 mm	161 mm	311 mm	130 g
BE-8945	T45	7.70 mm	150 mm	8 mm	36 mm	161 mm	311 mm	178 g

