

RF TERMINATION Type 6701.01.B

Description

Feed Through Termination, Low Power



Product Configuration

Connectors (side 1 / side 2) BNC plug (male) / BNC jack (female)
 Interface standards IEC 60169-8_MIL-STD-348A/301_CECC 22120

Technical Data

Electrical Data

Nominal Impedance 50 Ω
 Frequency range 0 to 1 GHz
 Frequency sub range DC to 0.1 GHz 0.1 to 0.5 GHz 0.5 to 1 GHz
 VSWR max. 1.05 1.1 1.25
 Power rating 0.4 Watt average power up to 70 °C ambient temperature, linearly derated to 0 Watt at 130 °C ambient temperature.

Mechanical Data

Weight 0.022 kg

Environmental Data

Operating temperature -40 °C to 130 °C
 2011/65/EC (RoHS) compliant

Material Data

Piece Part (side1)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Piece Part (side2)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Ordering Information

Single Packaging 6701.01.B
 Packaging

Additional Information

Remarks

DC resistance: 50 Ohm +/- 4 %