

**ARCA 604021**



Sample photo

**Order symbol:** ARCA 604021  
**Product nbr:** 8120012  
**Description:** Cabinet, PC  
**Remarks:** Grey cover, 2-point locking, hinges on the long side

**EAN:** 6418074079237  
**EI. number:**  
 Finland: 3423100  
 Denmark: 8212091100  
 Sweden: 2500118  
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.  
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		600	400	210	Ingress Protection (EN 60529): IP 66
<b>inch:</b>		23.6	15.7	8.3	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover colour:</b>		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>		PUR			<b>Certificates:</b>
<b>Temperatures:</b>					SGS Fimko
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
MPS ARCA 6040		Mounting plate			
MPP ARCA 6040		Mounting plate perforated			
MPX ARCA 6040		Mounting plate			
DRS ARCA 604021		DIN rail frame set			
DRS ARCA 604030		DIN rail frame set			
IDS ARCA 6040		Inner door set			
PMK ARCA 40		Pole mounting kit			

