

Elbow-length chemical gloves, delivering durable hand and arm protection

- **Fewer risks:** With no inner cotton flocking, AlphaTec[®] Solvex[®] 37-185 chemical-resistant gloves present lower lint contamination risks
- **Specialized protection:** Their high-performance nitrile compound composition grants them EN 374 Type A chemical protection, shielding up to the elbow
- **Improved durability:** This nitrile make-up also ensures EN and ANSI level 4 abrasion protection, making them suitable for heavy-duty cleaning
- **Elevated comfort:** AlphaTec[®] Solvex[®] 37-185 industrial gloves are also highly comfortable and dexterous
- **Food handling compliance:** They comply with both EU and FDA regulations for food handling



Industries

- Food Processing
- Metal fabrication
- Oil and gas
- Chemical
- Agriculture
- Automotive Aftermarket
- Utilities

Applications

- All food processing applications that have food contact
- Forging operations
- General pumping work
- Handling incoming goods
- Filling, blending and charging of raw materials
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Testing
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Painting or cleaning tools or robots

AlphaTec[®] Solvex[®]

37-185

Excellent chemical protection with a good level of grip, fit and comfort

Previously known as: Solvex[®] 37-185

Key Features

- **No cotton flocking:** PPE gloves with reduced lint contamination risks
- **Nitrile compound composition:** EN 374 Type A chemical resistance levels
- **Durable material:** ANSI and EN level 4 abrasion resistance

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec [®] Solvex [®] 37-185	N/A, Nitrile,	7, 8, 9, 10, 11	457 mm/ 18 inches	Green	• 1 pair/polybag; 12 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.