

Product data sheet

Item No. 92.232.4003.3

Cable assembly GST18I3K1B- 15 40GR01

gesis® Connection cable female - free end; length: 4m; type GST18I3; 3-pole; 250 V / 16 A; colour of coding: grey with grey strain-relief; cable: H05VV-F 3G1,5, colour: black



Item No.	92.232.4003.3
EAN	4015573680210
Order Unit	25 Piece(s)

Certificates / Approvals

Technical data
General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 2
Interlockable	Yes
Color of coding/ contact carrier	Pebble gray
Marking of poles	
Color of housing inclusive strain relief	Pebble gray

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F

Cable colour	Black
Cable diameter	8.3 mm
Version of cable	Female - free end
Type of cord set	Connection cable
Version cable end 1	GST18i3 socket
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	4 m
--------------	-----

Technical drawing

Kabel/cable H05VV-F3G1,5
Farbe/colour: siehe Tabelle/see table

.F	Farbe colour	Codierung *X*	Kabelfarbe cable colour
.1	schwarz black	N ⊕ L	schwarz black
.2	weiß white	N ⊕ L	weiß white
.3	grau grey	N ⊕ L	schwarz black
.5	rot red	N ⊕ L	schwarz black

Teile-Nr. part-no.	L	Beispiel (Farbe: schwarz) example (colour: black)	Typ type
92.232.XX03.F	XX in dm-Schritten	92.232.1003.1 = 10dm/L = 1000mm	GST1813K1B- 15 10SW
U2.232.XX03.F	XX in m-Schritten	U2.232.1203.1 = 12 m/L = 12000mm	GST1813K1B- 15 X12SW
92.232.XX93.F	XX in dm-Schritten	92.232.1093.1 = 10dm/L = 1000mm	

93.F = spezielle Verpackung und Etikettierung nach A 1960.000
special packaging and labelling according to A 1960.000

Freioleranz nach - General tolerance -

/	/	/	/	/	/
/	/	/	/	/	/
/	/	/	/	/	/
/	/	/	/	/	/

Weitere Daten siehe Katalog
further data see catalog

PRE-ASSEMBLED CABLE
KONFEKT_LEITUNG

Buchse/female - freies Ende/free end 1.5mm
Crimping/strapping/crimpersion: 81 250V