

Micrometer

Baked enamel-finished frame

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Baked enamel-finished frame

Delivery:

Including box, setting standard (from 25 mm), adjustment wrench, up to 50 mm with factory test certificate



Art. no.	32016 071
Brand	MITUTOYO
Manufacturer Part Number	103-165
Min./max. length measuring range	700-725 mm
Vernier scale	0.01 mm
Measuring surface diameter	8 mm
Measuring spindle increments	0.5 mm
Bracket depth	405 mm
Spindle clamping	Yes
Error limit	9 µm
Display	Nonius
Min./max. measurement force	5-15 N
Calibration Group	D
Gross Weight	11.000 kg
Product Group	3MA

EAN

4946368004327