

Mini temperature data logger starter kit

Model testo 174 T including USB interface and two further data loggers



Application:

Handy data logger with large display and measured data memory for 16,000 readings.

Execution:

- including USB interface for programming and reading out the data logger
- Starter set with three data loggers

Delivery:

3x mini data logger testo 174T, 1-channel, including wall bracket, USB interface for programming and reading out the mini data logger, PC software ComSoft Basic on CD-ROM, battery (6 x CR 2032 lithium) and calibration log



Art. no.	46200 220
Brand	TESTO
Manufacturer Part Number	0563 0561
Model	testo 174 T
Min./max. temperature measuring range	-30 to 70 °C
Digit increment (measuring instrument for temperature)	0.1 °C
Accuracy temperature	+/- 0,5°C at -20 to +70°C
Number of ducts	1 PCS
Data transmission type	USB
Measuring rate	1 measurements/min
Measured value memory	16000 measuring results
Hazard analysis and critical control points according to HACCP	HACCP compliant
IP protection class	IP 65
Colour	White
Material of housing	Plastic
Min./max. operating temperature	-30 to 70 °C
Battery designation	3V CR2032 Lithium
Number of rechargeable batteries/batteries	6 PCS
Channel type	Internal
Gross Weight	0.700 kg
Product Group	4CF

EAN

4029547023255