

## Jointed hose module

For MAXIFLEX® jointed hose systems



### Application:

For adjusting the length and position of the jointed hose system.

### Execution:

- Made from high-quality and robust plastic
- 1/4" version with 6.35 mm internal diameter
- 1/2" version with 12.7 mm internal diameter
- Max. 6 bar operating pressure

### Advantage:

- Coolant is supplied precisely where it is needed.
- Resistant to chemicals and solvents
- Not electrically conductive
- Can be shortened or extended as desired



<b>Art. no.</b>	<b>56495 025</b>
<b>Brand</b>	WIHA
<b>Manufacturer Part Number</b>	27086
<b>System design</b>	1/4 inch
<b>Type</b>	Jointed hose module, overall length 1000 mm
<b>Outlet diameter</b>	6.35 mm
<b>Included in delivery</b>	80 units
<b>Gross Weight</b>	0.125 kg
<b>Product Group</b>	575

### EAN

4010995270865