

## Power 250-10 W OF air compressor

metabo®

### Version:

- For single-phase alternating current
- Oil-free piston compressor
- Pressure reducer with manometer for controllable working pressure
- Instrument panel with easily legible manometers for tank and operating pressure
- Cord wrap facility
- Rubberised, robust wheels and handle for mobile applications
- Lifting eye for secure transport on construction sites

### Advantage:

- Push button with starter valve for reliable cold start
- Reduced service costs

### Delivery:

2 universal quick-release couplings



<b>Art. no.</b>	<b>75290 250</b>
<b>Model</b>	Power 250-10 W OF
<b>Operating pressure</b>	10 bar
<b>Intake air capacity</b>	220 l/min
<b>Delivery quantity effective at 80% max. pressure</b>	140 l/min
<b>Filling capacity</b>	120 l/min
<b>Tank capacity</b>	10 l
<b>Power input</b>	1.5 kW
<b>Max. rotation speed</b>	2850 rpm
<b>Length x width x height</b>	470 x 480 x 348 mm
<b>Weight</b>	21 kg
<b>With overload protection</b>	Yes

### EAN-Code

4007430244857