


REV.	DATE	DESCRIPTION
A	07/13/06	UPDATE DRAWING FORMAT



NO.	DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR MILLIMETERS ARE:	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR INCHES ARE:	APPROVALS	DATE	PART DESCRIPTION	DWG. NO.	REV.	SIZE	SCALE
8					0.5 - 8mm ± 0.20mm	.020 - .315 = ± 0.007"	DRAWN G.R.S.	07/13/06	SMA JACK TO SMA REVERSE POLARITY PLUG ADAPTER	132171RP-10	A	A	NA
7					8 - 30mm ± 0.40mm	.315 - 1.180 = ± 0.015"							
6					30 - 120mm ± 0.50mm	1.180 - 4.724 = ± 0.020"	CHECKED						
5							ISSUED						
4							SHEET	1 OF 1					
3	CONTACT PIN	BER. COPPER	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR MILLIMETERS ARE: UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR INCHES ARE: DO NOT SCALE DRAWING			CAD FILE C:/1732/132171RP-10.DWG					

Amphenol Connex

SMA JACK TO SMA REVERSE POLARITY PLUG ADAPTER

132171RP-10