



Baton 4 [PREMIUM EDITION]

DESIGNED TO STAND OUT

MAX OUTPUT	STANDARD MAX RUNTIME	PREMIUM MAX RUNTIME	MAX THROW
1,300 lumens	30 days	190 days	170 meters

*This information is for market reference only. Please do not make it public.



Regal Blue



Black



OD Green

Baton 4 [PREMIUM EDITION]

DESIGNED TO STAND OUT



MARKET APPLICATIONS

Camping & Hiking & Mountaineering & Household

UPC :

6975498003038 (Black)
6975498006411 (OD Green)
6975498006435 (Regal Blue)

DESCRIPTION

The Baton 4 Premium Edition includes the Baton 4 and a customized charging case. The Baton 4 is an upgraded version of the Baton 3. It features a high-performance LED and TIR lens, delivering an impressive maximum output of 1,300 lumens and a beam distance of 170 meters. The custom-designed charging case has a built-in 5000mAh 21700 battery, allowing you to fully charge the Baton 4 up to five times, providing up to 190 days of runtime for Baton 4. With enhanced performance and convenience, the Baton 4 Premium Edition is an ideal companion for all your lighting needs.



FEATURES

- **Small yet powerful light:** The Baton 4 delivers 1,300 lumens and has a beam distance of 170 meters. It's compact and high-performing, perfect for everyday carry.
- **Upgraded laser micro-perforated indicator:** The Baton 4 features laser micro-perforated indicators that intuitively shows the remaining brightness and battery life.
- **Durable metal switch:** The upgraded metal switch adds durability to the flashlight, making each press more solid and enjoyable.
- **Higher-capacity battery:** The charging case is equipped with a powerful 5000mAh battery, providing the Baton 4 with up to 190 days of runtime.
- **Command with the case:** Users can utilize the display button on the case to fully control the flashlight without needing to retrieve it.
- **Type-C input and output:** With its universal Type-C port, you can easily charge the case or use it as a power bank to charge your mobile devices.
- **Digital display button:** The case features a digital display button for precise battery level indication, allowing you to plan ahead for outdoor activities.
- **One Case for Five Lights:** The case is fully compatible with Baton 4 and Baton 3 and supports storing and charging the S1R II, Perun Mini, and Perun 2 Mini.
- **Reliable safety lanyard:** It comes with a secure safety lanyard to prevent accidental drops and ensure product safety.

OUTPUT

SPECIFICATIONS	Turbo	High	Medium	Low	Moonlight	STROBE
	1,300±600±300 lumens	600±300±60 lumens	60 lumens	12 lumens	0.5 lumens	13Hz at 1,300 lumens
	1.5+2.5+73 minutes	7+72+16 minutes	8 hours	35 hours	30 days	
	170 meters	110 meters	38 meters	18 meters	N/A	
	7,225 cd	3,025 cd	361 cd	81 cd	21 cd	

Specifications (Charging Case)	
Battery Capacity	3.6V 5000mAh
TYPE-C Input	5V 2A (MAX)
TYPE-C Output	5V 2.4A (MAX)
Output	4.2V 1A
Time to Charge Baton 4	1h
Time to Charge the Case	2.5h (Please use an adapter with a power output greater than 10W.)

* Note: All data above are test results according to ANSI / NEMA FL 1-2009 standards.

LIGHT SOURCE

High Performance CW LED

POWERED BY

Customized 650mAh battery (Baton 4);
5000mAh battery (Charging Case)

WEIGHT

6.84oz/194g (Including the case and the flashlight)

DIMENSIONS

Baton 4 Length: 2.48in/63mm Head Diameter: 0.83in/21mm Body Diameter: 0.83in/21mm	Charging Case Length: 2.56in/65mm Width: 1.26in/32mm Height: 3.46in/88mm
---	--

IN THE BOX

Baton 4 (Battery Included) x1
Baton 4 Charging Case x1
Lanyard (with pin tool) x1
Type-C USB Charging Cable x1
Cleaning Cloth x1
User Manual x1


WARRANTY

Baton 4 Flashlight:
Lifetime Warranty in the USA, Australia, Germany, France, and China.
5-Year Warranty in other countries and regions.
Charging Case: 2-Year Warranty.

BODY MATERIAL

Aluminum Alloy (Baton 4)
PC (Charging Case)

WATERPROOF IPX8



DROP TEST



COMPLIANCE



Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.