



Kvaser OBD II Extension Cable 5m

EAN: 73-30130-00301-9

Kvaser's OBD II Extension Cable is a highly durable extension cable of 5 metres in length with male to female [OBD II](#) connectors. The cable is made of high quality thermoplastic rubber to ensure excellent flexibility and resilience. All pins are connected.

Major Features

- Molded [OBD II](#) (SAE J1962) male connector, Type B (24 Volt).
- Molded OBD II (SAE J1962) female connector, Type B (24 Volt).
- Made of durable thermoplastic rubber.
- Gold plated pins on OBDII connectors for extra reliable contact.
- Termination is built in with a 120 Ohm terminating resistor.
- Available in other cable lengths.
- RoHS compliant.
- This cable can save wear and tear on your CAN interface's OBD2 connector.



Warranty

- 2-Year Warranty. See our General Conditions and Policies for details.

Support

- Free Technical Support on all products available by contacting support@kvaser.com.



TECHNICAL DATA - KVASER OBD II EXTENSION CABLE 5M

ON-BOARD BUFFER	N/A
MAXIMUM BITRATE (KBPS)	N/A
CB BOARD	No
ON-BOARD TX BUFFER	No
ON-BOARD TX BUFFER	N/A
ON-BOARD RX BUFFER	N/A
WIDTH (MM)	N/A
EMBEDDED SCRIPT	No
RUGGED	No
MAXIMUM BITRATE (KBPS)	N/A
# OF CAN CHANNELS	1
ON-BOARD RX BUFFER	No
OPERATING TEMPERATURE RANGE (C)	-30.00 to 85.00
IP CLASS	
PC INTERFACE	Cable
LENGTH (MM)	5000
# OF CAN CHANNELS	1
MSGRATE TX MAX	N/A
NETWORK CHANNEL(S)	
SILENT MODE	No
EMBEDDED SCRIPT	No
ERROR COUNTERS READING	N/A
CASING MATERIAL	Durable thermoplastic rubber
CAN FD	No
CURRENT CONSUMPTION	
WEIGHT (G)	600.0
STATUS	Active

Kvaser
Aminogatan 25 A SE 431 53 Mölndal SWEDEN
Kvaser Europe AB
Telephone: +46 31 886344
Email: sales@kvaser.com
<https://www.kvaser.com/>



Kvaser OBD II Extension Cable 5m

CB BOARD	No
DATABASE DBC SUPPORT	No
OPERATING SYSTEM	Win XP, Linux, Win 7, Win Vista, Win 10, Win 8
PC INTERFACE	Cable
API, FREE	N/A
MINIMUM BITRATE (KBPS)	N/A
CLOCK SYNC	No
GALVANIC ISOLATION	N/A
CERTIFICATIONS	CE, RoHS
NETWORK CHANNEL(S)	
CASING MATERIAL	
API, FREE	
OPERATING TEMPERATURE RANGE (C)	-30.00 to 85.00
MSGRATE RX MAX	N/A
CURRENT CONSUMPTION	N/A
STATUS	Active
SOUND	No
API, LICENCED	None
TIMESTAMP RESOLUTION (US)	N/A
IP CLASS	N/A
TIMESTAMP RESOLUTION (US)	N/A
OPERATING SYSTEM	Win XP, Linux, Win 7, Win Vista, Win 10, Win 8
ERROR FRAME GENERATION	No
CLOCK SYNC	N/A
HEIGHT (MM)	N/A
WEIGHT (G)	600.0
ON-BOARD BUFFER	No
SILENT MODE	N/A

Kvaser
Aminogatan 25 A SE 431 53 Mölndal SWEDEN
Kvaser Europe AB
Telephone: +46 31 886344
Email: sales@kvaser.com
<https://www.kvaser.com/>



Kvaser OBD II Extension Cable 5m

MINIMUM BITRATE (KBPS)	N/A
ERROR FRAME DETECTION	N/A
CONNECTOR	N/A
RUGGED	No
WIDTH (MM)	N/A
HEIGHT (MM)	N/A
ERROR FRAME GENERATION	N/A
ERROR COUNTERS READING	No
MSGRATE RX MAX	N/A
CONNECTOR	N/A
ERROR FRAME DETECTION	No
LENGTH (MM)	5000
GALVANIC ISOLATION	No
API, LICENCED	
CERTIFICATIONS	CE,RoHS
MSGRATE TX MAX	N/A
CAN FD	No
PRODUCT GROUPS	Cable
PRODUCT GROUPS	Cable
SOUND	N/A

The information herein is subject to change without notice