

80x80x25 mm (IP68)


33.0~60.0 CFM




Specifications

| Model | Bearing | Rating Voltage | Power Current | Power Consumption | Speed | Air Flow | Static Pressure | Noise | Weight | Curve |
|--------------------|--------------|----------------|---------------|-------------------|-------|----------|-------------------------|---------|--------|-------|
| | 2BALL Sleeve | (VDC) | (mA) | (WATTS) | (RPM) | (CFM) | (inch-H ₂ O) | (dB(A)) | (g) | |
| GF80251B1-000U-AE9 | ☉ | 12 | 330 | 3.96 | 4800 | 60.0 | 0.41 | 47.5 | 105.0 | 1 |
| GF80251B2-000U-AE9 | ☉ | 12 | 255 | 3.06 | 4500 | 57.0 | 0.35 | 46.0 | 105.0 | 2 |
| GF80251B3-000U-AE9 | ☉ | 12 | 200 | 2.40 | 4200 | 53.0 | 0.30 | 44.5 | 105.0 | 3 |
| GF80251B5-000U-AE9 | ☉ | 12 | 145 | 1.74 | 3200 | 41.0 | 0.18 | 33.0 | 87.0 | 4 |
| GF80251B6-000U-AE9 | ☉ | 12 | 120 | 1.44 | 2900 | 37.0 | 0.15 | 30.0 | 87.0 | 5 |
| GF80251B7-000U-AE9 | ☉ | 12 | 84 | 1.01 | 2600 | 33.0 | 0.11 | 28.0 | 87.0 | 6 |
| GE80252B1-000U-AE9 | ☉ | 24 | 200 | 4.80 | 4800 | 60.0 | 0.41 | 47.5 | 105.0 | 1 |
| GE80252B2-000U-AE9 | ☉ | 24 | 166 | 3.99 | 4500 | 57.0 | 0.35 | 46.0 | 105.0 | 2 |
| GE80252B3-000U-AE9 | ☉ | 24 | 137 | 3.29 | 4200 | 53.0 | 0.30 | 44.5 | 105.0 | 3 |
| GF80252B5-000U-AE9 | ☉ | 24 | 73 | 1.76 | 3200 | 41.0 | 0.18 | 33.0 | 87.0 | 4 |
| GF80252B6-000U-AE9 | ☉ | 24 | 59 | 1.42 | 2900 | 37.0 | 0.15 | 30.0 | 87.0 | 5 |
| GF80252B7-000U-AE9 | ☉ | 24 | 45 | 1.08 | 2600 | 33.0 | 0.11 | 28.0 | 87.0 | 6 |
| GE80254B1-000U-AE9 | ☉ | 48 | 114 | 5.48 | 4800 | 60.0 | 0.41 | 47.5 | 105.0 | 1 |
| GE80254B2-000U-AE9 | ☉ | 48 | 95 | 4.56 | 4500 | 57.0 | 0.35 | 46.0 | 105.0 | 2 |
| GE80254B3-000U-AE9 | ☉ | 48 | 75 | 3.60 | 4200 | 53.0 | 0.30 | 44.5 | 105.0 | 3 |

Air Flow-Static Pressure Characteristics



External dimensions(mm)



*All model could be customized. Please contact with Sunon Sales.

*Specifications are subject to change without notice. Please Visit SUNON website at www.sunon.com for update information.