




CONICAL FLASK

LabValue - Flasks, Conical Erlenmeyer with Narrow Neck



- » Conical flasks feature chemically resistant white graduated scale
- » Narrow Neck design
- » Uniform walls provide excellent strength against breakage
- » Borosilicate 3.3 glass has the following heat tolerances:
Strain Point -515°C | Annealing Point 565°C | Softening Point 820°C .

Code	Capacity	Pack Size
EGL0424C	50 ml	12
EGL0424D	100 ml	12
EGL0424F	250 ml	12
EGL0424G	500 ml	6
EGL0424H	1000 ml	6

