

## MTS single phase safety transformer


P: 160VA IN: 208...550VAC OUT: 24VAC

Single-phase - Control and Isolation Transformers  
160 VA  
Isolation class T 40/B


Other voltages on request.

### [Link to Product](#)

#### Illustration



stay connected



Product may differ from Image

### Input

Input voltage	208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550 V AC
Input current	0.87 A (208 V AC); 0.33 A (550 V AC)
Inrush current	16 A (208 V AC); 6.1 A (550 V AC)
Short-circuit current	14.5 A (208 V AC); 5.5 A (550 V AC)
Frequency	50...60 Hz

### General data

Standards	(EN 61558-1), (EN 61558-2-6), (EN 62041 category 0)
Test isolation voltage	6.3 kV (prim./sec.)
Mounting method	Key-hole mounting
Dimensions H × W × D	105×96×110
Fixing centers a × b × c	86.5×96×4.8
Drill hole Ø	4.8×8.4
Temperature range	-20...+40 °C (storage temperature -20...+80 °C)

### Output

Output voltage	24 V AC
----------------	---------

### Commercial data

country of origin	CZ
customs tariff number	85043180
minimum order quantity	1