

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191310014**  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** InsulKrimp Block Spade Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5), Length 19.80mm

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-009-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19131](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Solderless Terminals](#)  
 Product Name InsulKrimp  
 Type Spade Block  
 UPC 800753101371

**Physical**

Barrel Type Closed  
 Color - Resin Blue  
 Flammability 94V-0  
 Insulation PVC  
 Material - Plating Mating Tin  
 Net Weight 0.702/g  
 Packaging Type Bag  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Stud Size 10 (M5)  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 4.40mm max.  
 Wire Size AWG 14, 16  
 Wire Size mm<sup>2</sup> 1.30-2.00

**Material Info**

Engineering Number BB-2781-10X

**Reference - Drawing Numbers**

Product Specification PS-19902-009-001, PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19200-1001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19131 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description                                   | Product #                 |
|---|---------------------------|
| PremiumGrade Hand Crimp Tool                  | <a href="#">640010100</a> |
| Hand Crimp Tool                               | <a href="#">640010300</a> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <a href="#">640050100</a> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <a href="#">640050300</a> |