



The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKD XCKP XCMD XCKT

Associated body	ZCMD39L1 ZCT21N12 ZCD27 ZCMD21L5 ZCD35 ZCMD21C12 ZCD31 ZCT21G11 ZCMD25L5 ZCMD41L2 ZCP27 ZCMD29L1 ZCD26 ZCMD21L08U78 ZCP35 ZCT27P16 ZCMD29L5 ZCP28 ZCD25 ZCD21 ZCP37 ZCMD21L08R12 ZCMD81L1 ZCMD25L1 ZCT25G11 ZCT28G11 ZCMD29C12 ZCT26N12 ZCT27G11 ZCMD41L5 ZCMD21M12 ZCD37 ZCP29M12 ZCMD21L2 ZCT21P16 ZCD29M12 ZCMD37L2 ZCT26G11 ZCP29 ZCT28N12 ZCD28 ZCMD29L2 ZCMD21L1 ZCMD25L2 ZCMD81L2 ZCT25N12 ZCP21M12 ZCP21 ZCMD39L2 ZCMD61M12 ZCMD61C12 ZCMD81L5 ZCD39 ZCT28P16 ZCD29 ZCP39 ZCP25 ZCD21M12 ZCT27N12 ZCMD37L5 ZCT25P16 ZCP31 ZCMD37L1 ZCP26 ZCT26P16 ZCMD39L5 ZCMD41L1 ZCMD69C12
Movement of operating head	Linear
Type of operator	Roller lever plunger spring return thermoplastic
Type of approach	Lateral approach, 1 direction

### Complementary

Switch actuation	By 30° cam
Positive opening	With

## Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

## Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901298311
Nbr. of units in pkg.	1
Package weight(Lbs)	0.08 lb(US) (0.04 kg)
Returnability	Yes
Country of origin	ID

## Packing Units

Package 1 Height	0.200 dm
Package 1 width	0.350 dm
Package 1 Length	0.400 dm

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------