

Pneumatic module for 3 contacts



| Part number | 09 14 003 3501 |
|--------------------|-------------------------------------|
| Specification | Pneumatic module for 3 contacts |
| HARTING eCatalogue | https://b2b.harting.com/09140033501 |

Image is for illustration purposes only. Please refer to product description.

Identification

| Category | Modules |
|--------------------|-----------------------------------|
| Series | Han-Modular [®] |
| Type of module | Han [®] Pneumatic module |
| Size of the module | Single module |

Version

| Gender | Male Female |
|--------------------|-----------------------------------|
| Number of contacts | 3 |
| Details | Please order contacts separately. |

Technical characteristics

| Limiting temperature | -40 +85 °C |
|----------------------|------------|
| Mating cycles | ≥10,000 |

Material properties

| Material (insert) | Polycarbonate (PC) |
|---|--------------------|
| Colour (insert) | Blue |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | е |
| REACH Annex XVII substances | Not contained |



Material properties

| REACH ANNEX XIV substances | Not contained |
|-------------------------------------|------------------------------|
| REACH SVHC substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) R23 (HL 1-3) |

Specifications and approvals

| Specifications | IEC 61984 IEC 60664-1 |
|----------------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| Packaging size | 2 |
|--------------------------------|---|
| Net weight | 7.78 g |
| Country of origin | Germany |
| European customs tariff number | 39269097 |
| GTIN | 5713140162082 |
| ETIM | EC000438 |
| eCl@ss | 27440220 Module for industrial connectors (pneumatic) |