

Profile Recess 20

Profile Recess 20 EF/U7 1m anodised
0022587



Product features

- A recessed 1000mm length anodised aluminium lighting profile that can be combined with slide (0022614) or click (0022615) opal diffusers with a maximum LED strip width of 20mm and two mounting options (clips or plates). Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



PRODUCT OVERVIEW

Product name	Profile Recess 20 EF/U7 1m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278015
Warranty	3 years
Housing colour	Aluminium
Product EAN number	5410288225876

DATA TABLE

General data

Product name	Profile Recess 20 EF/U7 1m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278015
Warranty	3 years

Physical data

Housing colour	Aluminium
Nominal Product Length (mm)	1000
Nominal Product Width (mm)	30
Nominal Product Height (mm)	20.4
Weight (kg)	0.21

Packaging

Single packaging type	Carton
Product EAN number	5410288225876
Packaging single length / height (cm)	100.0

Profile Recess 20

Profile Recess 20 EF/U7 1m anodised

0022587

Packaging single width (cm)	2.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288225876
Units per outer package	35
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

TECHNICAL DRAWINGS

