

Twist drill set in box, type N HSS, steam-treated

For universal use up to 1000 N/mm²

ORION[®]

Application:

For drilling on hand-guided drills and CNC machines.

Execution:

- Twist drill with universal standard geometry, roll forged

Advantage:

- Long-term proven cutting geometry: excellent all-round properties and precise cutting behaviour
- Steam treatment ensures good adhesion to the drill and increases the service life

Art. no.	11043 051
Brand	ORION
Manufacturer Part Number	11043051
Composition of set	1,0-10,0
Pitch of drill diameter	0.5 mm
Number of pieces in assortment/set	19 PCS
Surface	Vaporised
Cutting material	HSS
Type	N, roll forged
DIN	338
Number of cutting edges	2 PCS
Gross Weight	0.550 kg
Product Group	1AP



EAN

4039247014705