

Adjustable clamps



Version:

- Heat-treated steel
- Painted

Art. no.	26120 040
Slot width	14 mm
Length	100 mm
Suitable cheese-head screw DIN 912	M12, M14
Section	21 mm
Slot length	40 mm
Clamping shoe height	20 mm
Clamping shoe width	40 mm
Width 3	14 mm
DIN	6314



EAN-Code

4020772070038