

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form

Art. no.	26195 030
Type	standard
Nominal dimension of groove	10 mm
Slot nut width	9.7 mm
Thread dimension	M8
Length	15 mm
Height	12 mm
Slot nut height	6 mm
DIN	508



EAN-Code

4020772080020