

electronic pocket vernier calipers

ABS shaft groove callipers with carbide-tipped measuring surfaces

Mitutoyo

Application:

For measuring shaft grooves.

Version:

- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- Carbide-tipped measuring faces
- Narrow measuring faces for difficult-to-reach measuring points

Delivery:

Delivered in box



Art. no.	32018 095
Min./max. length measuring range	0-150 mm
Min./max. length measuring range in inches	0-6 in
Data transmission type	DIGIMATIC
IP protection class	IP 67
With drive wheel	Yes
Error limit	0.001 in
Length of jaw	40 mm
Design	Metric, Imperial
Digit height	9 mm
Length of cross tips	16.5 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
Preset function	No
With mm / inch switching	Yes
With automatic shut off	Yes
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
Functions	Absolute function, ABS function, Origin (Dimension preset), Automatic switch-off

EAN-Code

4946368726892