

Electronic protractor

Angle 0–180°


ORION®

Application:

For measuring 0-180° angles

Version:

- Mobile measuring arm fixed using knurled thumb screw
- Adjust or set to zero on any flat surface
- 0.05 ° digit increment
- Made of stainless steel
- Error limit $\pm 0.3^\circ$
- Overhead display



Art. no.	38235 010
Limb length	150 mm
Degree arc diameter	120 mm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
Calibration Group	RD

EAN-Code

4053625047895