

Assembly workbench series V, with lowerable transport unit

With 3 drawers, 100% full extension, wheeled



Execution:

- Worktop made of solid beechwood, thickness 50 mm, sandable, glued in bars
- Robust, welded sheet steel construction
- Base made of square-section steel tube 45 x 45 x 2 mm, stationary, load capacity 1500 kg with evenly distributed load
- Vice, 100 mm jaw width with hinged lifter, can be rotated by 360° and height-adjustable
- Vice compartment fitted with one door which can be closed again after the vice has been folded out
- With lowerable transport unit, the drive/stop position is adjusted by simply turning the lever on the front side of the workbench

Advantage:

- Worktop with special tothing, therefore extremely robust and virtually unlimited service life
- Always mobile and ready for use anywhere thanks to transport unit



Art. no.	50284 829
Brand	ANKE
Manufacturer Part Number	999.021.0026
Working height	850 mm
Number of steering rollers	4 PCS
Worktop width	1270 mm
Number of drawers	3 PCS
Worktop height	50 mm
Number of doors	1 PCS
Worktop depth	700 mm
Pullout type	Full extension
On castors	Yes
Moving device, can be lowered	Yes
Colour of front	Optional
Cabinet colour	Optional
Model	706V
With single pull-out safety brake	Yes
Surface	Powder-coated
With wheel lock	No
Load-carrying capacity	1500 kg
Levelling	Yes
Dynamic load-carrying capacity	450 kg
Wheel diameter	100 mm
Type	mobile/retractable
Lock type	DOM® locking system
Material of worktop	Solid beech
Folding vice	Yes
Drawer front height	3 x 180 mm
Material	Sheet steel
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Gross Weight	139.073 kg
Product Group	502

EAN

4014641018726