

## Click-Torque torque wrench with reversible ratchet, adjustable

With calibration certificate, for clockwise and anti-clockwise tightening



### Execution:

- Setting: audible and perceptible click when scale values are reached
- Release mechanism: audible and perceptible click signal when the set torque is reached
- Very robust design, with reversible ratchet (45 teeth)
- Dual Nm and lbf-ft scale
- Fine adjustment scale in Nm - ensures precise and safe operation
- Ergonomically shaped 2-component handle
- Locking button on the end of the handle with silicone padding - protection against unintentional adjustment



<b>Art. no.</b>	<b>52261 400</b>
<b>Brand</b>	WERA
<b>Manufacturer Part Number</b>	05075625001
<b>Tip size</b>	1/2 inch
<b>Max. torque</b>	100 Nm
<b>Min. torque</b>	20 Nm
<b>Scale value torque</b>	0.5 Nm
<b>Length</b>	405 mm
<b>Min./max. torque</b>	20-100 Nm
<b>Error limit (%)</b>	3 %
<b>Calibration certificate</b>	Yes
<b>Gross Weight</b>	1.312 kg
<b>Product Group</b>	542

### EAN

4013288218926