

Electronic torque/angle-controlled wrench 7000-2 sTAC system

SmartTAC SYSTEM 1-1000 Nm, with Bluetooth interface



Application:

For highly precise screw connections

Execution:

- 3-fold signalling of the screwing process via acoustic signal (buzzer), vibration and all-round 360° LED display with 'traffic-light function' visible from any position
- Measured value display in 13 mm front size, incl. a pass/fail bolting rating
- Memory: for up to 3000 measurements, incl. date and time
- Large rotation angle range (adding) up to 999°
- Effective length for other plug-in tools adjustable/programmable
- Adjustable torque units: Nm, lbf ft, lbf in, kgf m
- Variable threshold value (first warning stage)
- Programmability of parameter sets and processes
- Control function: programmable torque control on rotation angle tightening and rotation angle control on torque tightening



Advantage:

- Large, high-contrast illuminated, easy-to-read OLED display, 180° rotatable
- Safety switch-on and switch-off function (2x button press) and automatic, time-dependent and energy-saving stand-by function
- USB socket for charging the battery directly on the tool
- Plug-in reversible ratchet included in scope of delivery

Delivery:

Includes plug-in reversible ratchets

Art. no.	52263 130
Brand	HAZET
Manufacturer Part Number	7291-2STAC
Min. torque	10 Nm
Max. torque	100 Nm
Min./max. torque	10-100 Nm
Torque measuring accuracy	+/- 1 %
Tip size	3/8 inch
Insert shank square	9 x 12 mm
Length	383 mm
Error limit (%)	1 %
Gross Weight	3.900 kg
Product Group	569

EAN

4000896223152