



050994-5-100

R2G4, 1.5mm², GREY

GeneralThin-walled car cable with PVC insulation and fine wire copper conductors for maximum 100°C conductor temperature.

Packaging (OD x Hub x Width):

Spool B3: 160mm x 56mm x 50mm

Structure:

Conductor: Blank stranded copper

Conductor insulation: PVC

Conductor identification: Multiple color combinations

Technical data:

Rating voltage: 100V

Temperature range: -40°C to +100°C (-40°F to +212°F)

Approvals: According to Volvo 7613 R2, 111 / 3



Product Properties:

Flame retardant

According to IEC/EN 60332-1-2

Single insulated/Double insulated

Single insulated

Dimensions:

Unit	m
MOQ	100 .

Approvals:

Approved according to CE	Yes
Approved according to Volvo R2 7613, 111/3	Yes
Flame retardant	According to IEC/EN 60332-1-2

Compliance:

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (235 Subs. 14 June 2023)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
Extended minerals	N/A, contains no extended minerals
CA Proposition 65	No CA Prop65
PFAS	No PFAS
POPs	No POPs

Other information:

Trademark	NEMIQ
ETIM-Class	EC003248 - Power cable < 1 kV, for permanent installation
ETIM-Release	7.0
Product Group	R2G4, Single Conductor, Red copper
Alternative SKU	050994-5-100

Logistic information:

Barcode	733117611526
Country of origin	SE
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	050994-5-100
Taric code	85444995
Unit	m
Units per parcel	801304
MOQ	100 .