



RMMD-2A/24VDC INPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 2 A

Input relay
1 relay; 2 NO contacts
24 V DC
Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image

Utilization category

AC-1	2 A (24 V AC; 110 V AC; 230 V AC)
AC-15	1 A (24 V AC); 0.1 A (230 V AC)
DC-13	0.8 A (24 V DC); 0.1 A (110 V DC); 0.01 A (230 V DC)

Input

Connection voltage - current	24 V DC (19.2...30 V DC) - 15 mA
Plug link (supplied)	Art.-Nr. 90960
LED display	LED (yellow)

General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	1.5 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+50 °C
Dimensions H × W × D	82×12×68 mm

Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 2 A
Min. load current	5 mA
Power rating (voltage dependent)	max. 250 VA/150 W
Switching frequency	max. 15 Hz
Contact material	Ag Au
Energize/release/contact bounce time	10/10/1 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1