


HT-30 - Horn Speaker



Miniature PA horn tweeter, 50 W, 8 Ohm

- Linear and wide bandwidth reproduction
- High power capability due to ferrofluid

Technical Data

Impedance (Z)	: 8 Ohm
Resonant frequency (fs)	: 2 kHz
Max. frequency range	: fx-20 kHz
Rec. crossov. frequ. (fmax.) (12 dB/oct.)	: 5 kHz
Music power	: 100 W _{MAX}
Power rating (P)	: 50 W _{RMS}
SPL (1 W/1 m)	: 98 dB
Radiation angle (vert./hor.)	: 60°/60°
Voice coil diameter	: 12 mm
Magnet diameter	: 50 mm
Mounting cutout	: Ø 59 mm
Mounting depth	: 47 mm
Dimensions	: 67x67 mm
Weight	: 0.19 kg