

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500107](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK 396 Crimp Terminal 2578, 22-26 AWG, Reel, Brass, 2.540µm Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [2578](#)
Application [Power, Wire-to-Board](#)
Crimp Quality Equipment [Yes](#)
Overview [KK® Interconnect System - Molex](#)
Packaging Alternative [08-50-0108 \(Loose\)](#)
Product Name [KK 396, KK 508](#)
UPC [800753759664](#)

Physical

Gender [Female](#)
Material - Metal [Brass](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.150/g](#)
Packaging Type [Reel](#)
Plating min - Mating [2.540µm](#)
Plating min - Termination [2.540µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [1.65mm max.](#)
Wire Size AWG [22, 24, 26](#)
Wire Size mm² [N/A](#)

Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Engineering Number [2578-\(P909\)](#)

Reference - Drawing Numbers

Packaging Specification [PK-2759-002-001](#)
Product Specification [PS-08-50-001](#)
Sales Drawing [SD-2578-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2578](#) Series

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,
[5239](#)