

Toledo Mirage A165

ToLEDo Mirage A165 105LM E27 SL
0029914



Product features

- A perfect choice for hospitality, decorative and mood lighting applications
- Unique and innovative lamp design and construction
- Low-lumen output to create the low-lit effect and gives no glare
- Low power construction: only 2.5W
- Perfect for SylPendant fixtures - a range of unique and elegant E27 lamp pendants, available in copper, brass, black and white finish
- Candlelight 2000K colour temperature creates a warm and cosy ambience
- High colour rendering - CRI80
- High quality, scratch and temperature resistant golden tinted glass envelope
- 25,000 hours of average rated life. Last 25 times longer than incandescent lamps
- Omni-directional light distribution
- Non-dimmable
- More than 100,000X switching cycles
- 3 years warranty



PRODUCT OVERVIEW

Product name	ToLEDo Mirage A165 105LM E27 SL
Technology	LED
Watt (Rated) (W)	2.5
Type	LED exchangeable
Cap/Base	E27
Fixture rating	Open
General application	Residential & Consumer
ETIM Class	EC001959
E-number FI	4740680
Warranty	3 years
Luminous flux (lm)	105
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Wattage (W)	2.5
Product Voltage (V)	230
Dimmable	No
Average life (Nominal) (h)	25000
Product EAN number	5410288299143

DATA TABLE

General data

Product name	ToLEDo Mirage A165 105LM E27 SL
Technology	LED
Watt (Rated) (W)	2.5

Toledo Mirage A165

ToLEDo Mirage A165 105LM E27 SL

0029914

Type	LED exchangeable
Cap/Base	E27
Fixture rating	Open
General application	Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740680
Warranty	3 years

Optical data

Luminous flux (lm)	105
Luminous flux (Rated) (lm)	105
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	2.5
Equivalent watt (W)	12
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
Control gear required	No
No. Of switching cycles before premature failures	>100000
Transformer required	No
Dimmable	No
Inrush Current (A)	0.2
Inrush Duration (µs)	8000
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	3
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Lifespan L70 B50	25000
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

Physical data

Nominal Product Length (mm)	303
Nominal Product Diameter (mm)	168
Weight (kg)	0.33

Toledo Mirage A165

ToLEDo Mirage A165 105LM E27 SL

0029914


Packaging

Single packaging type	Carton
Product EAN number	5410288299143
Packaging single length / height (cm)	33.0
Packaging single width (cm)	18.5
Packaging single depth (cm)	18.5
DUN14 (outer)	15410288299140
Units per outer package	2
Packaging outer length / height (cm)	38.5
Packaging outer width (cm)	20.0
Packaging outer depth (cm)	35.5

Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures


PHOTOMETRY




TECHNICAL DRAWINGS

SYLVANIA

Toledo Mirage A165
ToLEDo Mirage A165 105LM E27 SL
0029914



0029914



3
kWh/1000h




2019/2015

Toledo Mirage A165
ToLEDo Mirage A165 105LM E27 SL
0029914



0029914



3
kWh/1000h



2019/2015