



| | |
|-------------------------------|--|
| Category (ETIM): | Variable device mount |
| Type: | Device mount IP20-SDGVLB LED |
| Order number: | 18314506650 |
| Configuration: | Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10 |
| Operating device: | Electronic driver DALI (1 pcs.) |
| System performance (W): | 47 |
| Luminaire luminous flux (lm): | 7500 |
| lm/W: | 159 |
| Ambient temperatures: | 10°C / 40°C |
| Certifications: | IP 20, protection class I, F, DIN10500/Food, Indoor, CE |
| Colour of the housing: | traffic white RAL 9016 |
| Weight (net) (kg): | 2.1 |
| Dimensions LxWxH/DxH (mm): | 1531 x 63 x 46 |
| mounting method: | Mounting rail system mounting |
| EAN-number: | 4020863336203 |
| Commodity code: | 94051098 |


SDGVLB LED 7500lm 840 • vw • DALI • 18314506650



Lighting technology
Linear.Lens.Profil-direct wide distribution
SDGVLB LED 7500 lm 840



| | |
|----------------------------|-------------|
| η_{LB} | 100 % |
| lm/W | 159 |
| $\Phi \downarrow/\uparrow$ | 99 % / 1 % |
| UGR q/l | 23.7 / 27.9 |



Quick-fit mounting system Variable device mount; Device mount made of galvanised, profiled sheet steel, surface coated with polyester resin enamel. Toolless fastening with two integrated lateral lever locks. LED unit in housing length for optically seamless light run. Can be variably positioned on the mounting rail. Housing colour traffic white RAL 9016; Direct, wide light distribution using Linear.Lens.Profil made of matt PMMA plastic. Optically seamless light run. Heat-resistant cables including connection cable 1 m and rapid installation plug connector with tool-less phase pre-selection and locating finger.

Dimensions LxWxH/DxH (mm): 1531 x 63 x 46
Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm): 7500
lm/W: 159
Operating device: Electronic driver DALI (1 pcs.)
System performance (W): 47
Conditions: Suitable for use in ambient temperatures of 10°C to 40°C
Certifications: IP 20, protection class I, F, DIN10500/Food, Indoor, CE

Regiolux GmbH
Type: SDGVLB LED 7500 840 DALI vw
Article number: 18314506650
Product deep link: <http://www.regiolux.de/de/article/18314506650>
5 year guarantee after registration on website.