

ERGO series table trolley, load capacity 500 kg

Load areas 1000x700 mm and 1200x800 mm



Application:

Ideal for carrying out tasks at different heights or handling large and small products.

Execution:

- High-quality powder-coated, with MDF board
- Two fixed castors, two swivel castors with brake, castor diameter: 200 mm
- Spacing between the load areas: 580 mm
- Load capacity per load area: 250 kg
- 2 fixed castors and 2 swivel castors made of solid rubber 200x50 mm

Advantage:

- No need to go far to find your tools - work equipment is provided directly at the workstation
- Non-marking tyres



Art. no.	50291 457
Brand	KONGAMEK
Manufacturer Part Number	KM337-3B-ERGO
Load-carrying capacity	500 kg
Length	1110 mm
Length x width x height	1110 x 800 x 965 mm
Load-carrying capacity of loading surfaces	250 kg
ESD-capable	No
Number of loading surfaces	2
Loading surface size	1200 x 800 mm
Loading surface length	1200 mm
Loading-surface width	800 mm
Height	965 mm
Number of fixed rollers	2
Number of steering rollers	2
With wheel lock	Yes
Wheel diameter	200 mm
Material of wheel	TPE
Colour	Dark grey
Surface	Powder-coated
Gross Weight	46.500 kg
Product Group	5AT

EAN

7350112290329