



Power multicore cables CKPE50-ASAS-Mx

Cable assemblies Socapex 419 - Socapex 419 compatible connector with the length 5, 10, 20, 30, 40m

Norm conform, highly flexible cables with the reduced weight. Power multicore cables allow reduction of the cabling effort and cost. This cables are ideally suited for outdoor usage and demanding mobile applications.

Features & Benefits

- **Perfect handling** due to flexibility at low temperatures
- **Reduced weight** due to optimized cable diameter
- **Norm conform** multicore cables for the event technics (DIN 15765)

Market & Application

- Markets: Professional video wall, lighting, audio
- Mobile application: Festivals, live events
- Semi-permanent applications: Theaters, studios

Ordering information

Product title	Details	Length in m	Order code
CKPE50-ASAS-M050	Cable: Power multicore 13 x 2.5 mm ² black, connector 1: Socapex 419 female compatible, connector 2: Socapex 419 male compatible. Shrink tubing on both sides for your own labeling.	5	1029177
CKPE50-ASAS-M100		10	1029178
CKPE50-ASAS-M200		20	1029179
CKPE50-ASAS-M300		30	1029180
CKPE50-ASAS-M400		40	1029181

Technical Information

Product	
Product title	CKPE50-ASAS*
Gender	Male – Female
Connector type	LKS 19 (fully compatible with Socapex SL 419 series), 6 channels
Product type	Power multicore cables

Electrical	
Conductor resistance	7,98 Ω/km

Mechanical	
Lifetime	-
Locking device	Locking ring, compatible Socapex SL 419
Conductor cross section	2.5 mm ²
Outer diameter (OD)	16,8 mm
Weight	5.5 kg per 10m (without connector)
Bend radius	7,5 x OD mobile 4 x OD fix

Material	
Cable jacket type	PVC

Environmental

Standards compatibility	DIN 15765
Protection class	IP68 in mated condition
Temperature range	-5 °C to +70°C